


The Better Pex Header

Reduced/Closed Pex Headers

1"Pipe run, with 2,3,4,5,6,7,8,9,10,11,or 12

1/2"Crimpex (ASTM F877) fittings on **2"centres**.

Closed one end and reduced 3/4" female sweat on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002RC	1"	1/2" PEX	2	10
SX1005003RC	1"	1/2" PEX	3	10
SX1005004RC	1"	1/2" PEX	4	10
SX1005005RC	1"	1/2" PEX	5	10
SX1005006RC	1"	1/2" PEX	6	10
SX1005007RC	1"	1/2" PEX	7	10
SX1005008RC	1"	1/2" PEX	8	10
SX1005009RC	1"	1/2" PEX	9	10
SX1005010RC	1"	1/2" PEX	10	10
SX1005011RC	1"	1/2" PEX	11	10
SX1005012RC	1"	1/2" PEX	12	10

Plain/Closed Pex Headers

1"Pipe run with 2,3,4,5,6,7,8,9,10,11 or

12 1/2"Crimpex (ASTM F877) fittings on

2"centres.Closed one end and plain on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PL	1"	1/2" PEX	2	10
SX1005003PL	1"	1/2" PEX	3	10
SX1005004PL	1"	1/2" PEX	4	10
SX1005005PL	1"	1/2" PEX	5	10
SX1005006PL	1"	1/2" PEX	6	10
SX1005007PL	1"	1/2" PEX	7	10
SX1005008PL	1"	1/2" PEX	8	10
SX1005009PL	1"	1/2" PEX	9	10
SX1005010PL	1"	1/2" PEX	10	10
SX1005011PL	1"	1/2" PEX	11	10
SX1005012PL	1"	1/2" PEX	12	10

Closed/Pex Ends on Pex Headers

1"Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12
1/2"Crimpex (ASTM F877) fittings,**2"centres**.
Closed one end and 3/4"brass pex the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PC	1"	1/2" PEX	2	10
SX1005003PC	1"	1/2" PEX	3	10
SX1005004PC	1"	1/2" PEX	4	10
SX1005005PC	1"	1/2" PEX	5	10
SX1005006PC	1"	1/2" PEX	6	10
SX1005007PC	1"	1/2" PEX	7	10
SX1005008PC	1"	1/2" PEX	8	10
SX1005009PC	1"	1/2" PEX	9	10
SX1005010PC	1"	1/2" PEX	10	10
SX1005011PC	1"	1/2" PEX	11	10
SX1005012PC	1"	1/2" PEX	12	10

3/4" Pex at Each End of Pex Header

1"Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12 1/2" Crimpex (ASTM F877) fittings
on **2"centers** with 3/4"brass pex each end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PP	1"	1/2" PEX	2	10
SX1005003PP	1"	1/2" PEX	3	10
SX1005004PP	1"	1/2" PEX	4	10
SX1005005PP	1"	1/2" PEX	5	10
SX1005006PP	1"	1/2" PEX	6	10
SX1005007PP	1"	1/2" PEX	7	10
SX1005008PP	1"	1/2" PEX	8	10
SX1005009PP	1"	1/2" PEX	9	10
SX1005010PP	1"	1/2" PEX	10	10
SX1005011PP	1"	1/2" PEX	11	10
SX1005012PP	1"	1/2" PEX	12	10

Pex Shut Off Valve Headers

1"or 1 1/4"Pipe run with 2,3 or 4 1/2"Crimpex miniball valve expanded to coupling size one end and



plain the other end on **2"centres**.

<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
CVP1005002	1"	1/2"	2	5
CVP1005003	1"	1/2"	3	5
CVP1005004	1"	1/2"	4	5
CVP1255002	1 1/4 "	1/2"	2	4
CVP1255003	1 1/4 "	1/2"	3	4
CVP1255004	1 1/4 "	1/2"	4	4

Pex Balancing Valves Headers


1"or 1 1/4"Pipe run with 2,3 or 4 1/2"Crimpex miniball balancing valve.Expanded to coupling size one end and plain the other end on **2"centers**..



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
CVBP1005002	1"	1/2"	2	4
CVBP1005003	1"	1/2"	3	4
CVBP1005004	1"	1/2"	4	4
CVBP1255002	1 1/4 "	1/2"	2	4
CVBP1255003	1 1/4 "	1/2"	3	4
CVBP1255004	1 1/4 "	1/2"	4	4

[Click Here](#) for a Printable version of this page.

Alberta Custom Tee (2006) Ltd.
10037-96 Avenue
Westlock Alberta Canada T7P 2P9
PH: (780) 349-6511
Fax: (780) 349-4232



Home	Sales Reps and Distributors	72 inch Headers	Specialty Headers	End Caps, Reduced Ends & Tees
About Alberta Custom Tee	The Alberta Custom Tee Advantage	The Better Pex Header	Custom Extrusions	Outlet Tools

